

sections) for operation with restricted rial, e.g. up to 20 round or profile (capacity for 60 mm diameter mateactivation, run automatically. supervision. All sequences, including Automatic loading magazine



0.001° resolution). When an option recommended for automatic tailstock is used (an and B CNC axes (both with Machining with the help of A


ed with a central hole and then workpiece is milled smooth, providupwards 90°, the first side of the thin materials), the bar is tilted tilted back

headstock without interference, light-The large tool magazine, spindle






processor control system (for up to rate child's play. tions highly accunumber of opera-7 axes) make any




STAMA MC 535 SM



MC 530

last operation. workpiece is sepathen swivels 90° for the small stem. The unit rated except for a cutter, the finished Separating operation 1: Using a disc milling





cutter is cut away by a high-speed The material left by the disc milling Separating operation 2:

passed back along the chute for further processing. which is finished on 5 sides is

